



FEASA™ Low Light LED Analyser

Test Solution for Illuminated Switches

Introduction:



Automotive manufacturers are extensively using LED backlit switches and panels to create a safe and aesthetically pleasing cockpit environment for a car's occupants. Steering wheels are being designed with safety in mind to include more of the controls for in-car entertainment, phones and cruise control. Panels and switches with etched or painted symbols backlit with LEDs are nearly invisible during the day but give the driver better orientation and sense of space while driving at night.



Automotive manufacturers may source the various cockpit sub-assemblies from different suppliers. It is very important to have tight tolerances as well as standardised test set-ups to ensure correct colour matching and homogeneous intensity outputs of each sub-assembly. This ensures the consumer does not perceive colour and intensity non-uniformity in the end product.



Feasa's Low Light Led Analyser is the ideal solution for these applications. The extra sensitivity measures low light levels after the light has passed through an etched plastic panel.

Tests for:-

- ◆ Intensity
- ◆ Homogeneity of Parts
- ◆ xy Chromaticity
- ◆ Dominant Wavelength
- ◆ CCT

and all with the accuracy, reliability and speed that you have come to expect from the Feasa LED Test Solutions.

[Feasa Low Light Led Analyser](#)



Feasa Enterprises Ltd.

Castletroy • Limerick • Ireland

Telephone: + 353 61 330333 - Fax : + 353 61 330452 - Website: www.feasa.ie

Registered Office: Feasa Enterprises Limited, Holland Road, National Technology Park, Castletroy, Co.Limerick, Ireland.
Registered in Ireland, No. 106933. Copyright © 2011 Feasa Enterprises Limited. All rights reserved.

Page 1 of 2

Rev No.8.00 – 08th October, 2024



FEASA™ Low Light LED Analyser

Test Solution for Illuminated Switches

SPECIFICATIONS

ACCURACY xy Chromaticity	± 0.01 @ $x = 0.33, y = 0.33^1$ *Immediately after Calibration with a known source
OPTICAL Minimum Luminance Maximum Luminance	$< 0.5 \text{ cd/m}^2$ $< 1,000,000 \text{ cd/m}^2$
REPEATABILITY xy Chromaticity Intensity	± 0.002 $< 1\%$
ELECTRICAL USB Powered Serial, RS232, Daisy Chain	5V, 80mA
PHYSICAL Dimensions of 3, 5, 6 Channel Dimensions of 10 Channel	104.5mm x 54mm x 41mm* (L x W x H) 145mm x 54mm x 41mm* (L x W x H) * does not include bend radius of fiber
Fiber Length Fiber Diameter Minimum Bend Radius of Fiber	600mm 2.2mm OD with 1.5mm Single Core 30mm
Operating Temperature Range	0°C to +50°C
SOFTWARE GUI provided Sample command line interface C, C++ applications, examples dll, labview® support	

ORDERING INFORMATION:

Feasa 3 Channel Low Light
Feasa 5 Channel Low Light
Feasa 6 Channel Low Light
Feasa 10 Channel Low Light

Part No: Feasa 3A
Part No: Feasa 5A
Part No: Feasa 6A
Part No: Feasa 10A

Optical Heads

Part No: available upon request



Feasa Enterprises Ltd.

Castletroy • Limerick • Ireland

Telephone: + 353 61 330333 - Fax : + 353 61 330452 - Website: www.feasa.ie

Registered Office: Feasa Enterprises Limited, Holland Road, National Technology Park, Castletroy, Co.Limerick, Ireland.
Registered in Ireland, No. 106933. Copyright © 2011 Feasa Enterprises Limited. All rights reserved.